## **Technische Data Simplex400/450**



Sampler: Version with hand wheel

Seal: PTFE sealing cone, O-ring silicone (FDA approved)

Material: 1.4404 in contact with product; 1.4301 not in contact with product

Line pressure: from 0 to 12 bar

Line pressure surge: up to max. 20 bar without opening, depending on manual closing

pressure

Opening travel: approx. 5 mm

Flow size: Ø10 mm

Variation: different inputs and outputs as desired

Weight,

depending on version: 0,5 to 1,1Kg

Customs Id number: 8481 8019

Maintenance effort: max. 5 seals, time required for changing approx. 3-5 minutes

Simplex 400

Various input connections



## Simplex 450

Various input connections

